


HIGHLIGHTS


- Versatile suspension bar accessory
- Compatible with VTX A6 and VTX B15
- Used for suspension or pull-back applications
- Maximum Limit: (24) VTX A6/(15) VTX B15
- Lightweight design
- Shackle Size: 1/2 in

DESCRIPTION

The VTX A6 SB accessory is a lightweight suspension bar that can be used as an array frame or to implement pull-back of VTX A6 or B15 arrays. When used for pull-back, the suspension bar attaches to the bottom of an array and connects to a rear suspension point to allow for extra downtilt, otherwise not possible using the VTX A6 MF alone. The suspension bar can also attach to the top cabinet of an array and be used as an array frame. In this case, the downtilt angle is controlled by the number of cabinets and array geometry. Two suspension bars can be used for dual-point applications and added aiming flexibility: one at the top and one at the bottom of the array. The VTX A6 SB can support the weight of up to (24) VTX A6 or (15) VTX B15 enclosures (depending on array geometry). For more information about the suspension bar and use cases, refer to the **VTX A6 and VTX B15 Rigging Manuals**.



DIMENSIONS



TECHNICAL SPECIFICATIONS

PHYSICAL	
Construction :	High-grade steel with anti-corrosion coating
Finish :	Black powder coat
Compatible Shackle Size :	1/2-inch
Mechanical Limits¹	
Safe Limit :	(16) VTX A6 (10) VTX B15
Maximum :	(24) VTX A6 (15) VTX B15
Dimensions (H x W x D)²:	60 mm x 518 mm x 66 mm (2.4 in x 20.4 in x 2.6 in)
Net Weight³ :	1.7 kg (3.9 lbs)
Shipping Weight :	2.2 kg (4.8 lbs)
ORDERING INFORMATION	
SKU :	JBL-P3254MX VTX A6 SB
Included :	(1) Suspension bar (1) 1/2-inch Shackle #5118578

Footnotes:

1: Always check mechanical safety with JBL Line Array Calculator 3 software before use. For more information on Safe and Maximum Limits, refer to the **VTX A6 and VTX B15 Rigging Manuals**.

2: Refer to the 2D and 3D Customer Drawings for more detailed dimensions.

3: Weight includes the suspension bar only. Shackles and other rigging parts not included.

JBL continually engages in research related to product improvement. Some materials, production methods and design refinements are introduced into existing products without notice as a routine expression of that philosophy. For this reason, any current JBL product may differ in some respect from its published description, but will always equal or exceed the original design specifications unless otherwise stated.